

SPEAKMAN®

SE-604

SAFE-T-ZONE® EMERGENCY SHOWER AND EYE/FACE WASH DESCRIPTION

The SE-604 Safe-T-Zone® features a floor mounted emergency deluge shower and aerated eye/face wash combination unit. Shower is supplied with a NPTF stay open full flow ball valve, activated by a triangular pull handle eye/face wash is supplied with 1/2" open full flow ball valve, activated by a push handle.

SPECIFICATIONS

Showerhead: 8" Cicolac® yellow plastic

Flow Control: Internal 20 gpm regulator

Valve: 1" NPT female brass, chrome plated.

Full flow stay open ball valve.

Activator: Powder coated yellow, aluminum triangular pull rod

Stanchion: 1 1/4" IPS galvanized steel piping with brass fittings

Inlet & Waste: 1 1/4" NPT female

Finish: Dura Jade powder coated finish

Performance: 20 gpm @ 20 psi flowing

EYE WASH: SE-401

Bowl: Acrylic/pvc thermoplastic.

Spray Heads: (6) brass, chrome-plated aerated.

Valve: 1/2" NPT female brass, chrome-plated.

Activator: Stainless steel push handle.

Shrouds: Yellow polypropylene.

Inlet: 1/2" NPT female.


Strainer: Brass, chrome-plated in-line.

Compliance: ANSI Z358.1

Universal Emergency Sign Included

OPTIONS

- | | |
|--------------------------------|-----------------------------|
| <input type="checkbox"/> XPR | Extended pull rod |
| <input type="checkbox"/> FLW | Flow switch |
| <input type="checkbox"/> HS | Hand-held spray |
| <input type="checkbox"/> PC | Polished chrome showerhead |
| <input type="checkbox"/> BH | Brass showerhead |
| <input type="checkbox"/> SSH | Stainless steel shower hand |
| <input type="checkbox"/> FPV | Freeze protection valve |
| <input type="checkbox"/> SSBV1 | 1" stainless steel valve |
| <input type="checkbox"/> SSBV2 | 1/2" stainless steel valve |
| <input type="checkbox"/> TS | Top supply |
| <input type="checkbox"/> SPV | Scald protection valve |



Job Name _____
Location _____
Architect/Engineer _____
Sales Representative _____
Wholesaler _____
Date _____ Model # _____