

# model 8904

Laboratory Units

### **FEATURES & BENEFITS**

#### **SAFETY**

8" x 10-3/4" universal emergency sign make the unit easily detected in an emergency. Test card to record weekly checks helps maintain the unit?s best working quality.

#### **EYE/FACE WASH VALVE**

Valve is designed so full continuous flow occurs with the simple squeeze of a lever providing an easy start to the irrigation process.

#### HOSE

The 8' swivel hose delivers a wide coverage area and is pressure rated at 250 psi to further optimize durability.

#### MOUNTING

Counter-mounted design provides a practical and space efficient piece of emergency equipment.

#### **EYE/FACE WASH**

AXION MSR? eye/face wash head (patent pending) uses an inverted directional laminar flow to sweep contaminants away from the vulnerable nasal cavity.


#### **ANTIMICROBIALLY TREATED**

AXION MSR? eye/face head is antimicrobially treated using the natural protection of silver. Impregnating these components with silver helps protect the head against the growth of mold and mildew on the treated components. AXION MSR? is the only eye/face product on the market to feature antimicrobial protection.

# **OPTIONS**

- □ Vacuum Breaker: Model SP212 is a chrome-plated brass vacuum breaker.
- Repair Kit: Model VRKSP248 valve repair kit for Model SP248 squeeze handle valve.
- □ Tempered Water Blending Valves: Model 9201, thermostatic mixing valve that mixes hot and cold water for the tempering of eye/face wash units at a maximum flow rate of 20 gpm.
- □ Alarm: Model 9001.5, 120 VAC emergency alarm and light system. Buzzer and flashing light are activated by a 1/2" double pole, double throw flow switch.

To see all options for this model, visit www.hawsco.com



# **SPECIFICATIONS**

Model 8904 counter-mounted eye/face wash and body spray shall include an antimicrobially treated AXION MSR<sup>TM</sup> eye/face wash head to help protect against the growth of mold and mildew on the treated components, and shall feature inverted directional laminar flow which achieves zero vertical velocity supplied by an integral 3.7 gpm flow control. The unit shall also include a chrome plated brass stay-open squeeze lever valve, 8-foot 250 psi green hose with chrome-plated swivel fitting at one end, Noryl plastic deck flange with integral key slot for proper positioning of unit, universal sign, and 1/2" IPS inlet. In order to comply with state codes the use of a vacuum breaker is required with all hand held eye/face wash body spray units (Haws offers model SP212)

# **APPLICATIONS**

Perfect for the environment where safety is of the utmost importance and an extended coverage area may be needed. When installed properly, the functionally constructed, deck mounted design of the 8904 is space efficient.

Model 8904 is certified by CSA & IAPMO to meet the ANSI Z358.1-2004 Standard for Emergency Eyewash and Shower Equipment.